Data Sheet

Receiver 26A005



Description

Subminiature magnetic receiver (Balanced Armature Type) for use in In The Canal and Completely In the Canal applications with standard response


Features

- Great ITE, ITC and CIC applications
- High output, maximum peak output 126 dB
- Improved shock performance

Mechanical data

Weight 0.17 gr. Case material Ni80Fe15Mo5 Solder pad material Sn96.5Ag3.0Cu0.5 **Dimensions** Refer to outline drawing

Product drawing - Dimensions in mm [inch]



Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible. Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.

+45 4630 6666 USA: +1 952 543 8300 PRC: +86 512 6832 3401 NL: +31 20 6068 100



Data Sheet

Receiver 26A005



Specifications

Acoustic loading: 10.0 mm of 1.0 mm diameter tubing into a 2 cc coupler.

Constant current drive of 3.32 mA RMS (0.55 mVA @ 1000 Hz).

Environmental conditions: 23 °C (73.4F), 50% RH.

Parameters		Min	Тур	Max	Unit	Comments
Sensitivity	@ 200 Hz	98.5	101.5	104.5	dB	
	@ 500 Hz	99	102	105	dB	
	@ 1000 Hz	101	104	107	dB	
Peak 1	frequency	2000	2175	2400	Hz	
	output	113	116	119	dB	
Valley 1	frequency	3500	4250	5000	Hz	
	output	100	102.5		dB	
Peak 2	frequency	5000	5500	6000	Hz	
	output	104	107	110	dB	
THD	@ 1/3 peak			5	%	
	@ 1/2 peak			5	%	
Maximum output @ peak frequency				126	dB	@ 50 mVA input

Electric parameters	Min	Тур	Max	Unit	Comments
Impedance @ 1000 Hz	40	50	60	Ohm	
DC resistance @ 20°C	20	24	28	Ohm	
DC bias current range	zero bias				

Additional parameters	Min	Тур	Max	Unit	Comments
Shock resistance	14000			g	90% survival rate with THD @ 1/2 peak frequency < 10%
Storage temperature range	-40		63	°C	

A positive voltage applied to the negative terminal (-) will result in an increase in pressure at the sound outlet.

Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible. Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.

DK: +45 4630 6666 USA: +1 952 543 8300 PRC: +86 512 6832 3401 NL: +31 20 6068 100




Data Sheet

Receiver 26A005



Typical response curveSolid curve: Ideal current source 3.32 mA RMS. Dashed curve: Ideal voltage source 0.17 V RMS.



Sonion reserves the right to make changes at any time to improve reliability, function or design, in order to provide the best product possible. Receivers series of this type can produce very high sound pressure levels. When such receivers are applied in hearing instruments or other communications equipment special attention should be paid to this capacity in order to prevent possible hearing damage.

DK: +45 4630 6666 USA: +1 952 543 8300 PRC: +86 512 6832 3401 NL: +31 20 6068 100

